

Silencer UOM-1/4

Part number: 538432

FESTO



[PDF](#) [General operating condition](#)

Data sheet

Feature	Value
Type of seal on screwed plug	No seal
Mounting position	optional
Design	Open silencer
Symbol	00991473
Operating pressure vacuum generator	0 bar ... 8 bar
Operating pressure of vacuum generator	0 MPa ... 0.8 MPa
Operating pressure of vacuum generator	0 psi ... 116 psi
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C ... 60 °C
Type of mounting	Screw-in
Product weight	11.1 g
Pneumatic connection	G1/4
Material shock absorber insert	PU foam
Material screwed plug	POM
Material housing	POM
Material inner tube	Wrought aluminium alloy