

AS-i module ASI-4DI3DO-M12X2-5POL-Z

Part number: 542125

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
CE mark (see declaration of conformity)	To EU EMC Directive To EU Explosion Protection Directive (ATEX) In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
KC mark	KC-EMV
Approval	c UL us listed (OL)
Explosion protection	Zone 2 (ATEX) Zone 2 (UKEX) Zone 22 (ATEX) Zone 22 (UKEX)
ATEX category gas	II 3G
ATEX category dust	II 3D
Explosion protection certification outside the EU	EPL Dc (GB) EPL Gc (GB)
Explosion ignition protection type for gas	Ex ec IIC T4 Gc X
Explosion ignition protection type for dust	Ex tc IIIC T115°C IP67 Dc X
Explosion ambient temperature	-5°C ≤ Ta ≤ +50°C