


Silencer UOS-1

Part number: 552252

FESTO



[PDF](#) [General operating condition](#)

Data sheet

Feature	Value
Type of seal on screwed plug	No seal
Mounting position	Any
Design	Open silencer
Symbol	00992064
Operating pressure	0 MPa ... 1 MPa
Operating pressure	0 bar ... 10 bar
Operating medium	Compressed air to ISO 8573-1:2010 [-:::]
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Sound pressure level	75 dB(A)
Ambient temperature	-10 °C ... 50 °C
Type of mounting	With male thread
Product weight	200 g
Pneumatic connection	G1
Material shock absorber insert	Packaging unit
Note on materials	RoHS compliant
Material housing	POM
Material sleeve	Wrought aluminium alloy