

Bellows kit DADB-S1-20-S301-350

Part number: 553419

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Outside diameter	29 mm
Size	20
Stroke range	301 mm ... 350 mm
Piston rod extension	101 mm
Design	Round
Mounting position	optional
Design	With ducted exhaust air
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper, zinc or nickel are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils.
Media resistance	Dust Chips Oils Grease Petrol
Ambient temperature	-10 °C ... 80 °C
Product weight	100 g
Type of mounting	Via threaded pin Via female thread
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material adapter components	PA-reinforced
Material seals	NBR
Material bellows	NBR
Material threaded pin	High-alloy stainless steel