

Coupling EAMD-56-46-24-23X27

Part number: 558005

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting diameter 1	24 mm
Mounting diameter 2	23 mm
Size	56
Nominal length	46.5 mm
Mounting position	Any
Max. rotational speed	5500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	151 kgmm ²
Transmittable torque	60 Nm
Product weight	409 g
Note on materials	RoHS compliant