

# Coupling EAMC-56-58-24-25

Part number: 558316

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Mounting diameter 1	24 mm
Mounting diameter 2	25 mm
Size	56
Nominal length	58 mm
Mounting position	Any
Max. rotational speed	5500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	128 kgmm <sup>2</sup>
Transmittable torque	60 Nm
Product weight	265 g
Note on materials	RoHS compliant