

Push-in sleeve NPQM-D-S6-E-P10

Part number: 558812

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|---|
| Size | Standard |
| Nominal size | 4 mm |
| Design | Straight design |
| Size of pack | 10 |
| Operating pressure complete temperature range | -0.095 MPa ... 1.6 MPa |
| Operating pressure complete temperature range | -0.95 bar ... 16 bar |
| Operating pressure complete temperature range | -13.775 psi ... 232 psi |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:-:-] |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 °C ... 70 °C |
| Product weight | 5.5 g |
| Pneumatic connection, port 1 | Push-in sleeve Ø 6 mm |
| Pneumatic connection, port 2 | Push-in sleeve QS-6 |
| Note on materials | RoHS compliant |
| Material housing | Brass, nickel-plated |