

Push-in sleeve NPQM-D-S8-E-P10

Part number: 558813

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	Standard
Nominal size	6 mm
Design	Straight design
Size of pack	10
Operating pressure complete temperature range	-0.095 MPa ... 1.6 MPa
Operating pressure complete temperature range	-0.95 bar ... 16 bar
Operating pressure complete temperature range	-13.775 psi ... 232 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C ... 70 °C
Product weight	7.5 g
Pneumatic connection, port 1	Push-in sleeve QS-8
Pneumatic connection, port 2	Push-in sleeve QS-8
Note on materials	RoHS compliant
Material housing	Brass, nickel-plated