

# Push-in sleeve NPQM-D-S10-E-P10

Part number: 558814

FESTO



 [General operating condition](#)

## Data sheet

| Feature                                       | Value                                    |
|---|--|
| Size  | Standard                                 |
| Nominal size                                  | 8 mm                                     |
| Design  | Straight design                          |
| Size of pack                                  | 10                                       |
| Operating pressure complete temperature range | -0.095 MPa ... 1.6 MPa                   |
| Operating pressure complete temperature range | -0.95 bar ... 16 bar                     |
| Operating pressure complete temperature range | -13.775 psi ... 232 psi                  |
| Operating medium                              | Compressed air to ISO 8573-1:2010 [7::-] |
| Note on operating and pilot medium            | Lubricated operation possible            |
| Corrosion resistance class CRC                | 1 - Low corrosion stress                 |
| LABS (PWIS) conformity                        | VDMA24364-B1/B2-L                        |
| Ambient temperature                           | -20 °C ... 70 °C                         |
| Product weight                                | 11 g                                     |
| Pneumatic connection, port 1                  | Push-in sleeve QS-10                     |
| Pneumatic connection, port 2                  | Push-in sleeve QS-10                     |
| Note on materials                             | RoHS compliant                           |
| Material housing                              | Brass, nickel-plated                     |