

Coupling EAMC-20-30-5-6

Part number: 558902

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting diameter 1	5 mm
Mounting diameter 2	6 mm
Size	20
Nominal length	30 mm
Mounting position	Any
Max. rotational speed	9000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	1.06 kgmm ²
Transmittable torque	2.2 Nm
Product weight	20 g
Note on materials	RoHS compliant