

Connecting cable VMPAL-KM-S-SD44-IP67-10

Part number: 560427

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--------------------------------------|
| Product weight | 1577 g |
| Electrical connection | Cable with plug |
| Cable length | 10 m |
| Cable characteristic | Standard |
| Min. cable bending radius | 115 mm |
| Cable diameter | 9.6 mm |
| Cable structure | 36 x 0.25 mm ² |
| Degree of protection | IP67 To IEC 60529 |
| Ambient temperature with moving cable | -5 °C ... 80 °C |
| CE mark (see declaration of conformity) | In accordance with EU RoHS Directive |
| UKCA marking (see declaration of conformity) | To UK RoHS instructions |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Note on materials | RoHS compliant |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| Material cable sheath | PVC |