


End plate VABE-S6-2RZ-G34

Part number: 560839

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Based on standard	ISO 5599-2
Mounting position	optional
Terminal type	44
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	336 g
Pilot air port 12	G1/4
Pilot air port 14	G1/4
Pneumatic connection, port 1	G3/4
Pneumatic connection, port 3	G3/4
Pneumatic connection, port 5	G3/4
Note on materials	RoHS-compliant
Material end plate	Die-cast aluminium