

# Coupling EAMD-16-15-6.35-8X10

Part number: 561292

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Mounting diameter 1	6.35 mm
Mounting diameter 2	8 mm
Size	16
Nominal length	15 mm
Mounting position	Any
Max. rotational speed	10000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	0.355 kgmm <sup>2</sup>
Transmittable torque	1.6 Nm
Product weight	12.8 g
Note on materials	RoHS compliant