

Coupling EAMD-25-22-6.35-10X12

Part number: 561293

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting diameter 1	6.35 mm
Mounting diameter 2	10 mm
Size	25
Nominal length	22 mm
Mounting position	Any
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	3.2 kgmm ²
Transmittable torque	3.6 Nm
Product weight	43.7 g
Note on materials	RoHS compliant