

# Coupling EAMC-16-20-5-5

Part number: 562676

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Mounting diameter 1	5 mm
Mounting diameter 2	5 mm
Size	16
Nominal length	20 mm
Mounting position	optional
Max. rotational speed	10000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	0.28 kgmm <sup>2</sup>
Transmittable torque	1.1 Nm
Product weight	8 g
Note on materials	RoHS-compliant