

Coupling EAMC-16-20-5-8

Part number: 562677

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|------------------------|------------------------|
| Mounting diameter 1 | 5 mm |
| Mounting diameter 2 | 8 mm |
| Size | 16 |
| Nominal length | 20 mm |
| Mounting position | optional |
| Max. rotational speed | 10000 rpm |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -25 °C ... 60 °C |
| Relative air humidity | 0 - 95% |
| Ambient temperature | -25 °C ... 60 °C |
| Mass moment of inertia | 0.28 kgmm ² |
| Transmittable torque | 1.1 Nm |
| Product weight | 8 g |
| Note on materials | RoHS-compliant |