

# Branching module MS9-FRM-G-VS-Y

Part number: 564147

FESTO



 General operating condition

## Data sheet

Feature	Value
Size	9
Series	MS
Mounting position	optional
Design	Branching module
Symbol	00991510
Operating pressure	0 bar ... 12 bar
Operational voltage range AC	0 V ... 250 V
Operational voltage range DC	0 V ... 125 V
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 7 according to ISO 14644-1
Storage temperature	-10 °C ... 60 °C
Media temperature	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Product weight	1100 g
Type of mounting	Either: Front panel mounting In-line installation With accessories
Pneumatic connection, port 3	G1
Pneumatic connection, port 4	G1
Material covering	PA-reinforced
Note on materials	RoHS-compliant
Material sub-base	Die-cast aluminium
Material mounting bracket	Die-cast aluminium
Material housing	Die-cast aluminium
Material module connector	Die-cast aluminium