

Electrical sub-base CAPC-F1-E-M12

Part number: 570042

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Dimensions (W x L x H)	50 x 148 x 28 mm
Field bus interface	2x M12 bushing 5-pin
Operational voltage range DC	18 V ... 30 V
Max. power supply	4 A
Nominal operating voltage DC	24 V
Approval	c UL us listed (OL)
Corrosion resistance class CRC	2 - Moderate corrosion stress
Storage temperature	-20 °C ... 70 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Degree of protection	IP65 IP67
Ambient temperature	0 °C ... 50 °C
Product weight	85 g
Cable length	20 m
Note on materials	RoHS-compliant
Material housing	PA