

# Bus interface CDPX-F-CO

Part number: 575301

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Mounting depth	24 mm
Height	91 mm
Length	41 mm
Approval	C-Tick c UL us - Listed (Oil)
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C ... 70 °C
Relative air humidity	5 - 85% Non-condensing
Degree of protection	IP20
Ambient temperature	0 °C ... 50 °C
Product weight	150 g
Note on materials	RoHS compliant
Fieldbus interface	CANopen
Field bus interface, connection system	Plug Sub-D 9-pin
Field bus interface, transmission rate	9.6 kbit/s to 1 Mbit/s