

Electrical adapter SASC-P4-A-M8-A

Part number: 8000326

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP40
Electrical connection 1, connection type	Plugs
Electrical connection 1, cable outlet	Straight, angled
Electrical connection 1, connector system	M8x1, A-coded, to EN 61076-2-104 Diameter 8 mm, A-coded to EN 61076-2-104
Electrical connection 1, number of connections/cores	4
Electrical connection 1, used connections/cores	4
Electrical connection 1, type of mounting	Snap-locking Screw-type lock Not rotatable
Electrical connection 1, compatible type of mounting	Compatible with latching lock Compatible with rotatable screw-type lock
Type of mounting	Threaded
Housing colour	Black
Note on materials	RoHS-compliant
Material housing	PA-reinforced
Material screws	High-alloy steel