

Control cable NEBC-S1G25-K-3.2-N-LE25

Part number: 8001373

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Electrical connection	25-pin Straight plug connector/open at one end Sub-D/-
Shielding	yes
Cable length	3.2 m
Cable diameter	7 mm
Degree of protection	IP40 In assembled state
CE mark (see declaration of conformity)	In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364 zone III
Note on materials	RoHS-compliant
Corrosion resistance class CRC	0 - No corrosion stress
Cable sheath colour	Grey
Housing colour	grey