

Shock absorber DYEF-G8-M4-Y1

Part number: 8073902

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	M4
Stroke	0.9 mm
Cushioning	Elastic cushioning rings/pads at both ends without metal fixed stop
Mounting position	Any
Position detection	None
Max. impact speed	0.8 m/s
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C ... 60 °C
Cushioning length	0.9 mm
Max. tightening torque	0.5 Nm
Max. energy consumption per stroke	0.018 J
Product weight	5 g
Type of mounting	Via threaded sleeve
Note on materials	RoHS compliant
Material seals	NBR
Material housing	High-alloy steel