

Inverting cap DHAS-GA-B22-S

Part number: 8097634

FESTO



Data sheet

 [General operating condition](#)

| Feature | Value |
|--|---|
| Inverting cap version | Standard |
| Note on operating and pilot medium | Observe resistance of materials that come into contact with the media |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Ambient temperature | -40 °C ... 180 °C |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke | 189 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 158 N |
| Product weight | 18 g |
| Note on materials | RoHS-compliant |
| Material cap | VMQ (silicone) |