


Quick exhaust valve SE-1/8-B

Part number: 9685

FESTO



 General operating condition

Data sheet

| Feature | Value |
|---|--|
| Valve function | Quick exhaust |
| Selection of additional functions | With silencer |
| Pneumatic connection, port 1 | G1/8 |
| Pneumatic connection, port 2 | G1/8 |
| Type of mounting | Screw-in |
| Standard nominal flow rate, exhaust 0.6-0.5 MPa (6-5 bar, 87-72.5 psi) | 660 l/min |
| Standard nominal flow rate, air flow 0.6-0.5 MPa (6-5 bar, 87-72.5 psi) | 300 l/min |
| Operating pressure | 0.5 bar ... 10 bar |
| Ambient temperature | -20 °C ... 75 °C |
| Material housing | Die-cast zinc |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Nominal size | 5 mm |
| Mounting position | optional |
| Symbol | 00991459 |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Media temperature | -20 °C ... 75 °C |
| Sound pressure level | 100 dB(A) |
| Product weight | 75 g |
| Pneumatic connection, port 3 | G1/8 |
| Material seals | NBR |