


Pressure indicator OH-10

Part number: 9791

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Symbol	00991500
Operating pressure	0.14 MPa ... 0.8 MPa
Operating pressure	1.4 bar ... 8 bar
Operating pressure	20.3 psi ... 116 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 80 °C
Product weight	4 g
Pneumatic connection	Barbed fitting PK-3
Note on materials	RoHS-compliant