


Swivel lever valve RW/O-3-PK-3

Part number: 10750

FESTO



[General operating condition](#)

Data sheet

| Feature | Value |
|---|---|
| Valve function | 3/2-way, monostable, open/closed |
| Type of actuation | Mechanical |
| Standard nominal flow rate (standardised to DIN 1343) | 80 l/min |
| pneumatic working port | PK-3 |
| Operating pressure | 0 bar ... 8 bar |
| Design | Piston seat |
| Nominal size | 2.5 mm |
| Type of piloting | Direct |
| Symbol | 00991285 |
| Operating medium | Compressed air to ISO 8573-1:2010 [-:-:-] |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C ... 60 °C |
| Type of mounting | With through-hole |
| Pneumatic connection, port 1 | PK-3 |
| Pneumatic connection, port 2 | PK-3 |
| Pneumatic connection, port 3 | PK-3 |
| Material seals | NBR |
| Material housing | POM |