

Solenoid valve MFH-3-1/8-SEU

Part number: 11121

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Valve function	3/2-way, closed, monostable
pneumatic working port	G1/8
Operating pressure	0.5 bar ... 8 bar
Degree of protection	IP65
Symbol	00991308
LABS (PWIS) conformity	VDMA24364-B2-L
Pneumatic connection, port 1	G1/8
Pneumatic connection, port 2	G1/8
Pneumatic connection, port 3	G1/8
Note on materials	RoHS-compliant