

Clevis foot CRLNG-63

Part number: 161843

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	63
Based on standard	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Mounting position	optional
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Ambient temperature	-40 °C ... 80 °C
Max. load capacity	4 kN
Product weight	370 g
Note on materials	RoHS-compliant
Material mounting	Electropolished High-alloy steel
Material bearing	Polymer