


Silencer U-3/8

Part number: 2309

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|------------------------------------|---|
| Mounting position | optional |
| Symbol | 00991473 |
| Operating pressure | 0 MPa ... 1 MPa |
| Operating pressure | 0 bar ... 10 bar |
| Flow rate to atmosphere | 6000 l/min |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:-:-] |
| Note on operating and pilot medium | Lubricated operation possible |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Sound pressure level | 82 dB(A) |
| Ambient temperature | -10 °C ... 70 °C |
| Product weight | 29.6 g |
| Pneumatic connection | G3/8 |
| Material shock absorber insert | PE |
| Note on materials | RoHS-compliant |