

Union nut MCK-PK-9

Part number: 2967

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	Female thread M16x1
Operating pressure complete temperature range	0 MPa ... 1 MPa
Operating pressure complete temperature range	0 bar ... 10 bar
Operating pressure complete temperature range	0 psi ... 145 psi
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-C1-L
Ambient temperature	-10 °C ... 60 °C
Pneumatic connection, port 1	For barbed fitting inside diameter of 9 mm with union nut
Material union nut	Wrought aluminium alloy, anodised
Note on materials	RoHS-compliant