


Time delay valve VZOB-3-1/4

Part number: 3489

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Symbol	00995773
Operating pressure	0 MPa ... 1 MPa
Operating pressure	0 bar ... 10 bar
Standard nominal flow rate (standardised to DIN 1343)	600 l/min
Adjustable delay time	0 s ... 30 s
Explosion protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B2-L
Type of mounting	With through-hole
Pneumatic connection	G1/8 G1/4
Note on materials	RoHS-compliant