

# Solenoid coil MSW-230AC

Part number: 3592

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Type of actuation	Electrical
Mounting position	Any
Min. pick-up time	10 ms
Duty cycle	100%
Insulation material class	F
Characteristic coil data	230 V AC: 50 Hz, pick-up power 30 VA, holding power 22 VA
Permissible voltage fluctuations	+/-10%
CE mark (see declaration of conformity)	To EU Low Voltage Directive
UKCA marking (see declaration of conformity)	To UK regulations for electrical equipment
LABS (PWIS) conformity	VDMA24364-C1-L
Storage temperature	-10 °C ... 60 °C
Degree of protection	IP65
Ambient temperature	-5 °C ... 50 °C
Product weight	175 g
Electrical connection	Type A Plug To EN 175301-803
Type of mounting	External hex 1/8 Retaining clip
Note on materials	RoHS compliant
Material solenoid coil	Duroplast
Material electrical contact	Tin-plated brass
Material winding	Copper