

Barbed hose fitting N-3/8-P-6

Part number: 3608

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Nominal size | 4.5 mm |
| Type of seal on screwed plug | Sealing ring |
| Mounting position | optional |
| Design | Straight design |
| Size of pack | 1 |
| Operating pressure complete temperature range | -0.95 bar ... 16 bar |
| Operating medium | Compressed air to ISO 8573-1:2010 [7::-:] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C ... 60 °C |
| Max. tightening torque | 15 Nm |
| Product weight | 8.71 g |
| Pneumatic connection, port 1 | Male thread G3/8 |
| Pneumatic connection, port 2 | For tubing I.D. 6 mm |
| Note on materials | RoHS-compliant |
| Material housing | Anodised aluminium |