

# Pressure indicator OH-22-RT

Part number: 4131

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Mounting position	optional
Symbol	00991500
Operating pressure	1.4 bar ... 8 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	-10 °C ... 45 °C
Ambient temperature	-10 °C ... 45 °C
Product weight	25 g
Type of mounting	Installation into control panel in Ø22.5
Pneumatic connection	G1/8
Note on materials	RoHS-compliant