


Silencer UOS-1

Part number: 552252

FESTO



[PDF](#) [General operating condition](#)

Data sheet

| Feature | Value |
|--------------------------------|--|
| Type of seal on screwed plug | No seal |
| Mounting position | optional |
| Design | Open silencer |
| Symbol | 00992064 |
| Operating pressure | 0 MPa ... 1 MPa |
| Operating pressure | 0 bar ... 10 bar |
| Operating medium | Compressed air to ISO 8573-1:2010 [-:::] |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Sound pressure level | 75 dB(A) |
| Ambient temperature | -10 °C ... 50 °C |
| Type of mounting | Via male thread |
| Product weight | 200 g |
| Pneumatic connection | G1 |
| Material shock absorber insert | PE |
| Note on materials | RoHS-compliant |
| Material housing | POM |
| Material sleeve | Wrought aluminium alloy |