




solenoid valve MOFH-3-1/2

Cikkszám: 7884

FESTO



 [Általános üzemi körülmények](#)

[→ Support Portal](#)

Termék-megbízhatósági adatlap

The information in this "Product reliability data sheet" is based on products being used as intended. This includes complying with all specifications in data sheets, catalogues, user documentation and the general operating conditions. The user alone is responsible for determining whether a product is suitable for a particular application.

Jellemző	Érték
Well-tried component ¹⁾	Yes
Service-life value B ₁₀ ²⁾	5 Mio cycles
Design characteristics	Mechanical spring return Not free of overlap
Lap	Underlap
Max. positive test pulse with 0 signal	2.200 µs
Max. negative test pulse with 1 signal	3.700 µs

- 1) The product is a well-tried product for a safety-related application according to ISO 13849-1. The relevant basic and well-tried safety principles according ISO 13849-2 for this product are fulfilled. The suitability of the product for a precise application must be verified and confirmed by the user.
- 2) The ascertainment of characteristic service life values is generally based on the ISO 19973 "Pneumatic fluid power - Assessment of component reliability by testing".