

# Angle seat valve

## VZXF-L-M22C-M-B-G1-240-M1-V4V4T-50-10

FESTO

Part number: 1002517



[PDF](#) General operating condition

### Data sheet

Feature	Value
Design	Poppet valve with piston drive
Type of actuation	Pneumatic
Sealing principle	Soft
Mounting position	Any
Type of mounting	Inline installation
Line connection	Threaded coupling G1 to DIN ISO 228
Nominal size	24 mm
Valve function	2/2-way, single solenoid, closed
Flow direction	Non-reversible
Medium pressure	0 MPa ... 1 MPa
Medium pressure	0 bar ... 10 bar
Nominal pressure PN	40
Exhaust-air function	Cannot be throttled
Type of reset	Mechanical spring
Type of piloting	Externally actuated
Pneumatic connection	Female thread G1/8
Operating pressure	0.6 MPa ... 1 MPa
Operating pressure	6 bar ... 10 bar
Operating pressure	87 psi ... 145 psi
Symbol	00991367
Medium	Vapour Mineral oil-based hydraulic fluid Inert gases Mineral oil Water Filtered compressed air, grade of filtration 200 µm Neutral fluids
Direction of flow	Below valve seat, for gaseous and liquid media
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Max. viscosity	600 mm <sup>2</sup> /s
Media temperature	-40 °C ... 200 °C
Ambient temperature	-10 °C ... 60 °C
Flow rate Kv	11 m <sup>3</sup> /h
Note on materials	RoHS compliant
LABS (PWIS) conformity	VDMA24364 zone III
Material process valve housing	Cast stainless steel
Material number process valve housing	1,4408

<b>Feature</b>	<b>Value</b>
Material spindle seal	PTFE
Material seat seal	PTFE
Product weight	1600 g
Corrosion resistance class CRC	3 - high corrosion stress
Material drive housing	High-alloy stainless steel