

# Solenoid coil MSN1G-24DC-OD

Part number: 123060

FESTO



 [General operating condition](#)

## Data sheet

| Feature                          | Value  |
|----------------------------------|--|
| Mounting position                | optional   |
| Min. pick-up time                | 10 ms  |
| Duty cycle                       | 100%   |
| Characteristic coil data         | 24 V DC: 2.5 W                                     |
| Permissible voltage fluctuations | -15%/+10%  |
| Approval                         | c UL us - Recognized (OL)                          |
| LABS (PWIS) conformity           | VDMA24364-C1-L                                     |
| Media temperature                | -10 °C ... 50 °C                                   |
| Degree of protection             | IP65   |
| Ambient temperature              | -10 °C ... 50 °C                                   |
| Product weight                   | 80 g   |
| Electrical connection            | 3-pin<br>Type A<br>To DIN EN 175301-803            |
| Type of mounting                 | Clamped<br>Via retaining clamp<br>With accessories |
| Material housing                 | PA   |
| Material electrical contact      | Steel  |
| Material winding                 | Copper   |