

# Timer PZVT-300-SEC

Part number: 150239

FESTO



 General operating condition

## Data sheet

Feature	Value
Design	Mechanical sequence counter with pneumatic drive
Switch-off pressure	≤0.1 bar
Operating pressure	2 bar ... 6 bar
Switch-on pressure	≥1.6 bar
Standard nominal flow rate (standardised to DIN 1343)	50 l/min
Adjustable delay time	20 s ... 300 s
Adjustment accuracy	± 6 s
Pause duration for reset	≥200 ms
Repetition accuracy of time setting	± 3 s
Explosion protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation not possible
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP54 With protective cap and panel frame To IEC 60529
Ambient temperature	-10 °C ... 60 °C
Product weight	45 g
Type of mounting	Front panel mounting
Pneumatic connection	Female thread M5
Note on materials	RoHS-compliant
Material housing	ABS