

# Mounting kit SMBR-8-40

Part number: 175098

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	40
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper, zinc or nickel are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils.
Ambient temperature	-20 °C ... 70 °C
Material profile	Wrought aluminium alloy
Note on materials	RoHS-compliant
Material retaining bracket	POM