

# Silencer UC-QS-8H

Part number: 175611

FESTO



[PDF](#) [General operating condition](#)

## Data sheet

| Feature                            | Value                                     |
|------------------------------------|---|
| Mounting position                  | optional                                  |
| Size of pack                       | 1   |
| Symbol                             | 00991473                                  |
| Operating pressure                 | 0 MPa ... 1 MPa                           |
| Operating pressure                 | 0 bar ... 10 bar                          |
| Flow rate to atmosphere            | 1500 l/min                                |
| Operating medium                   | Compressed air to ISO 8573-1:2010 [7::-:] |
| Note on operating and pilot medium | Lubricated operation possible             |
| LABS (PWIS) conformity             | VDMA24364-B1/B2-L                         |
| Sound pressure level               | 60 dB(A)                                  |
| Ambient temperature                | -10 °C ... 70 °C                          |
| Product weight                     | 2.3 g                                     |
| Pneumatic connection               | QS-8                                      |
| Material shock absorber insert     | PE  |
| Material screwed plug              | PE  |
| Note on materials                  | RoHS-compliant                            |