

Plastic tubing PLN-6X1-NT

Part number: 193404

FESTO



 General operating condition

Data sheet

| Feature | Value |
|---|--|
| Outside diameter | 6 mm |
| Flow-relevant bending radius | 32 mm |
| Inside diameter | 4 mm |
| Min. bending radius | 11 mm |
| Temperature-dependent operating pressure | -0.095 MPa ... 1.4 MPa |
| Temperature-dependent operating pressure | -0.95 bar ... 14 bar |
| Temperature-dependent operating pressure | -13.775 psi ... 203 psi |
| Note on operating pressure | Wasser: max. 0,8 MPa bei 0 - 50 °C |
| Approval | German Technical Control Board (TÜV) |
| Certificate issuing authority | B 013277 0527 00 |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free) |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Cleanroom suitability, measured according to ISO 14644-14 | Element installed statically, no meaningful evaluation possible according to ISO 14644-1 |
| Suitable for use with food | See supplementary material information |
| Ambient temperature | -30 °C ... 80 °C |
| Product weight according to length | 0.0147 kg/m |
| Pneumatic connection | For push-in connector O.D. 6 mm For barbed fitting I.D. 4 mm with union nut For barbed fitting I.D. 4 mm |
| Colour | Natural |
| Note on materials | RoHS compliant |
| Material tubing | Packaging unit |