

Lubricator MS6-LOE-3/8-R

Part number: 529783

FESTO



[PDF General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Size | 6 |
| Series | MS |
| Mounting position | Vertical +/-5° |
| Design | Proportional standard mist lubricator |
| Max. oil capacity | 75 cm ³ |
| Bowl guard | Plastic bowl guard |
| Symbol | 00991532 |
| Operating pressure | 1 bar ... 16 bar |
| Min. flow rate for lubricator function | 50 l/min |
| Standard nominal flow rate (standardised to DIN 1343) | 5300 l/min |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] Inert gas |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Storage temperature | -10 °C ... 60 °C |
| Suitable for use with food | See supplementary material information |
| Media temperature | -10 °C ... 60 °C |
| Oil viscosity | ISO VG 32 |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 600 g |
| Type of mounting | With accessories |
| Pneumatic connection, port 1 | G3/8 |
| Pneumatic connection, port 2 | G3/8 |
| Note on materials | RoHS-compliant |
| Material housing | Die-cast aluminium |
| Material bowl | PC |