

Sub-base VMPA1-FB-AP-4-1

Part number: 533352

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--------------------------------|-------------------------|
| Width | 42 mm |
| Length | 107.3 mm |
| Grid dimension | 10.5 mm |
| Max. number of valve positions | 4 |
| Operating pressure | -0.9 bar ... 10 bar |
| Pilot pressure | 3 bar ... 8 bar |
| Corrosion resistance class CRC | 0 - No corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -5 °C ... 50 °C |
| Product weight | 185 g |
| Pneumatic connection, port 2 | M7 |
| Pneumatic connection, port 4 | M7 |
| Note on materials | RoHS-compliant |
| Material sub-base | Die-cast aluminium |