

Vacuum filter VAF-DB-3/8

Part number: 553140

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------|---|
| Mounting position | Vertical |
| Grade of filtration | 80 µm |
| Symbol | 00991483 |
| Operating pressure | -0.95 bar ... 0 bar |
| Note on operating pressure | Only for use in open vacuum systems |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:-:-] |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Ambient temperature | -5 °C ... 50 °C |
| Max. tightening torque | 15.3 Nm |
| Product weight | 156 g |
| Type of mounting | Via wall/surface bracket |
| Pneumatic connection | G3/8 |
| Vacuum connection | G3/8 |
| Note on materials | RoHS-compliant |
| Material seals | NBR |
| Material filter | PE |
| Material housing | PP reinforced |
| Material bowl | PA |
| Suitable for ejector pulse | ≤7 bar |