


Time delay valve VZO-3-PK-3

Part number: 5754

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|---|
| Nominal size | 2 mm |
| Type of actuation | Pneumatic |
| Design | Poppet valve with spring return |
| Symbol | 00991131 |
| lap | Underlap |
| Note on forced dynamization | Switching frequency min. 1/week |
| Operating pressure | 2.5 bar ... 8 bar |
| Standard nominal flow rate (standardised to DIN 1343) | 60 l/min |
| Adjustable delay time | 0.25 s ... 5 s |
| Pause duration for reset | ≥50 ms |
| Repetition accuracy of time setting | ± 0.5 s |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation not possible |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Pilot medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 150 g |
| Type of mounting | On mounting frame |
| Pneumatic connection | PK-3 |
| Material housing | Die-cast zinc |