

Distributor block FR-4-1/2-B

Part number: 6704

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal size	18.6 mm
Mounting position	Any
Operating pressure complete temperature range	0 bar ... 16 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7::-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 80 °C
Product weight	120 g
Number of outputs	3
Number of supply lines	1
Pneumatic connection, port 1	Female thread G1/2
Pneumatic connection, port 2	Female thread G1/2
Note on materials	RoHS compliant
Material housing	Die-cast aluminium