

# Adapter AD-1/2NPT-G1/2-I

FESTO

Part number: 9627



 [General operating condition](#)

## Data sheet

Feature	Value
Nominal size	14.3 mm
Operating pressure complete temperature range	-0.95 bar ... 10 bar
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Max. tightening torque pneumatic connection 1	28 Nm
Max. tightening torque pneumatic connection 2	40 Nm
Product weight	48.48 g
Pneumatic connection, port 1	Male thread 1/2 NPT
Pneumatic connection, port 2	Female thread G1/2
Note on materials	RoHS-compliant
Material seals	PVC
Material housing	Galvanised steel