

# Quickstepper FSS-12-C

**FESTO**



## Controlling sequences entirely with pneumatics:

### The Festo Quickstepper.

Where purely pneumatic, simultaneous control of up to 12 steps as well as several movements is required, Festo's Quickstepper is right at home.

It's highly convincing thanks to:

- Integrated control panel for easy, reliable programming
- Easy installation on Festo 2n frames, or front panel mounting
- Optional safety cover with lock prevents unauthorised tampering
- No special fittings required; pneumatic connection via barbed connectors
- Clear-cut labelling of pneumatic inputs and outputs
- Simple, logical programming according to displacement-step diagrams
- No need for programming tools

The Festo FSSC-12 Commander can be used as an actuator. It features the same installation advantages as the Quickstepper. And the Quickstepper fits neatly into the rest of Festo's broad product range.



Purely pneumatic

Easy programming

12 steps ahead

**810.1.PSI** →

Product Short Information

# Quickstepper FSS-12-C



Technical Data	
Number of steps	Max. 12
Number of outputs	12
Number of inputs	12
Pressure range	2.5 to 6 bar
Medium	Filtered compressed air (5 µm), unlubricated
Temperature range	-15 to +60 °C in dry air
Connections	
Supply air P	4 mm barbed connector
Inputs	3 mm barbed connector
Auto/reset L/MAN/P	3 mm barbed connector
Material	Housing: ABS Sub-base: PA 12
Mounting	Festo 2n mounting frame or front panel
Panel cutout	92 x 92 mm
Protection	IP20
Protection with lockable cover and rubber sealing plate	IP54

The Quickstepper is maintenance-free!

## Festo AG & Co. KG

Ruiter Strasse 82  
73734 Esslingen  
Internet [www.festo.com](http://www.festo.com)  
Tel. ++49 (0)711 347-0  
Fax ++49 (0)711 347-2144  
E-mail [service\\_international@festo.com](mailto:service_international@festo.com)

Subject to change

180504