

Rod clevis SGA-M12X1,25

Part number: 10767

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--------------------------------|--------------------------|
| Size | M12x1.25 |
| Radial deviation +/- | 5 mm |
| Angle compensation +/- | 120 deg |
| Mounting position | optional |
| Threaded connection | Male thread M12x1.25 |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -40 °C ... 150 °C |
| Max. load capacity | 1.5 kN |
| Product weight | 222 g |
| Note on materials | RoHS-compliant |
| Material bolt | Galvanised steel |
| Material rod eye | Steel Galvanised |
| Material lock | Spring steel, galvanised |